

AHFA Advocacy at Work

Start each day reviewing *Legiscan* and other regulation/bill tracking platforms Receive *heads – up email* from a member company or Solution Partner First Read and analysis/research Form AHFA Task Group and Circulate for Ideas/Input Initial outreach to agency and bill sponsors Initial outreach to other affected trade associations to build like-minded coalitions – strength in numbers Task Group Meeting to Review and Discuss 'Next Steps' First Pen of letter or comments to agency/bill sponsor Circulate to task group for input, edits, and ideas Final letter or comments to agency, bill sponsor, and State AG

AHFA Advocacy at Work

Start working with the Agency to better understand the regulation from their perspective and engage them regarding *implementation challenges* for the industry. Task Group develops 'Industry Best Practices' to demonstrate compliance. Zoom meetings with UDAF staff Second Coalition Letter to staff + State AG detailing suggested revisions. UDAF staff visit to NC - plant tours and meetings with AFHA task group mbrs AHFA Ground Game in Salt Lake City Local retailer, Dutko, Local contact, AHFA meeting with staff in Utah AHFA meeting with Utah staff and CA @ IABFLO - Best Practices Meetings with Legislature and Agency Commissioner + UDAF staff Agency stay, revocation, and revised regulatory language

AHAF Advocacy at Work

New Regulation with New implementation Date AHFA Best Practices Incorporated into the New Proposed Regulation **Open Comment Period** Continued meetings with UDAF staff **Provide Written Comments + Best Practices Slide Deck Review Proposed Final Regulation** Utah Ground Game if Needed AHFA Member Education and Communication Collaboration with AHFA Solution Partners **Continued Partnership with UDAF - Implementation/Enforcement** Now on to CA/Paddock Model for other State Programs

UDAF · TAGGING LAW REGULATION 4




Utah Department of Agriculture and Food Online Point of Purchase Consumer Right to Know Law – R70-101 Industry Best Practice

Industry Best Practice

Instead of using an image of the law label, an alternative approach is to present the law label information in text format as a glossary of terms as described in this slide deck, i.e., Slide 6. The Industry Best Practice

incorporates *clearly* identifiable hyperlinks directing consumers to information describing the product's filling materials. This link is labeled *filling material descriptions, a*nd lead to a dedicated page outlining all the necessary details describing the product's filling materials, e.g., a glossary of terms.

Industry Best Practice



Hyperlink to Potential Filling Materials Description/Glossary of Terms Page

Hyperlink to List of URN and Sterilization numbers where applicable

List of URN and Sterilization Numbers

Industry Best Practice Sample Generic Descriptions of Possible Cushion Filling Materials

SEAT CUSHION CONSTRUCTION

Comfort Crown Medium Firm	A superior cushion of fine high density & resiliency foam. The core is laminated	
	with a soft foam cap contour cut with a permanently built in crown. It is	
	wrapped in a layer of 1 oz polyester fiber providing excellent durability.	
	The cushion is characterized by a firmer, more tailored look.	
	(Can order EXTRA FIRM by adding notation "Extra Firm" on the order.)	
Essential Comfort Firm STD	Constructed of a fine grade of firm compression, high resiliency foam.	
	The core is laminated with a soft foam cap that is contour cut with a	
	permanently built in crown. The cushion is then wrapped in a layer	
	of soft compression poly foam. It is characterized by a firmer,	
	more tailored look.	
Essential Comfort Soft	Constructed of a fine grade of medium compression, high resiliency	
	foam. The core is laminated with a soft foam cap that is contour cut	
	with a permanently built in crown. The cushion is wrapped in a layer	
	of soft compression poly foam. It is characterized by a firmer,	
	more tailored look.	
Elegance Plush Medium	A relaxed, deep seating cushion constructed with a core of high	
	resiliency foam. The core is laminated with a 2" layer of softer foam-	
	wrap material on each side with a built in crown insert sandwiched	
	in between & then wrapped in a layer of Dacron fiber & inserted	
	into a down proof ticking. The result is a very soft, relaxed look &	
	feel with some comfort wrinkles.	
1	I	

Industry Best Practice – Company URN and Sterilization Numbers (as appropriate)

Registration Number	Sterilization Numbers
CA 40328 (VN)	
VA 16871 (CN)	
UT 3931 (VN)	
RI 1611 (ID)	
CA 3854 (IN)	
CA 46514 (VN)	
UT 6490 (CA)	
CA 41146 (VN)	
UT 5047 (MX)	
VA 593 (VA)	PA 6251